

A T 2 4 C S 0 1 - S S H M - B

Product Family

24CS = Serial EEPROM, plus
128-bit Serial Number

Device Density

01= 1 Kilobit
02= 2 Kilobit

Shipping Carrier Option

B = Bulk (Tubes)
T = Tape and Reel, Standard Quantity Option
E = Tape and Reel, Extended Quantity Option

Operating Voltage

M = 1.7V to 5.5V

**Device Grade or
Wafer/Die Thickness**

H or U = Industrial Temperature Range
(-40°C to +85°C)
11 = 11mil Wafer Thickness

Package Option

SS = SOIC
X = TSSOP
MA = 2.0mm x 3.0mm UDFN
ST = SOT23
WWU = Wafer Unsaun