

**A T 2 4 C M 0 2 - S S H D - B**

**Product Family**

24C = Standard I<sup>2</sup>C-compatible  
Serial EEPROM

**Device Density**

M = Megabit Family  
02 = 2 Megabit

**Shipping Carrier Option**

B = Bulk (Tubes)

T = Tape and Reel, Standard Quantity Option

**Operating Voltage**

D = 2.5V to 5.5V

M = 1.7V to 5.5V

**Device Grade or  
Wafer/Die Thickness**

H or U = Industrial Temperature Range  
(-40°C to +85°C)

11 = 11mil Wafer Thickness

**Package Option**

SS = SOIC

U2 = WLCSP

WWU = Wafer Unsawn