

Custom Name	TIMER		
Generate Initializer Code	Initialize all registers		
▼ Hardware Settings			
Timer Enable	☐		?
Run Standby Mode	☐		?
Timer Mode	16 Bit (Normal)		?
Clock Select	System Clock / 64		?
Clock Frequency	375	kHz	?
Count Direction	UP		?
Requested Period	2.66667 μ s $\leq$ 50	ms	$\leq$ 174.76267ms
?			
Actual Period	50	ms	
Count on Event Input A	☐		?
Count on Event Input B	☐		?
Event Action A	CNT_POSEDGE		?
Event Action B	NONE		?
► Waveform Generation Settings			
▼ Interrupt Settings			
Overflow Interrupt Enable	☒		?
Compare Channel 0 Interrupt Enable	☐		
Compare Channel 1 Interrupt Enable	☐		
Compare Channel 2 Interrupt Enable	☐		
Generate ISR	☒		