

▶ Toolbar ⓘ

Easy View Register Initialization ⓘ

▼ Software Settings

API PrefixRTC

▼ Hardware Settings

Enable RTC☒

RTC Clock Source Selection1.024 kHz from OSC32K

RTC Clock (Hz)1024

External Clock (Hz) $1 \leq 32768 \leq 32768$

Prescaling FactorRTC Clock / 1

Compare (s) $0 \leq 0.5 \leq 64$

Actual Compare499 ms

Period (s) $0 \leq 5 \leq 64$

Actual Period4.999 s

Run in debug☐

▼ Periodic Interrupt Timer

PIT Enable☐

Period SelectionOff

Run in debug☐

▼ Interrupt Settings

Compare Match Interrupt Enable☒

Overflow Interrupt Enable☐

Periodic Interrupt Enable☐