

? API Prefix: OPAMP

▼ Global Settings

? Enable OPAMP System:

? Run in Debug Mode:

? Input Range: Full Input Range

? Time Base (cycles): $1 \leq 23 \leq 127$

▼ Hardware Settings

? Select Mode: Single OPAMPs

? Enable OP0:

? OP0 Configuration: Voltage Follower

? Enable OP1:

? OP1 Configuration: Voltage Follower

? Enable OP2:

? OP2 Configuration: Voltage Follower