

SDMMC1




Matched Net Lengths [Tolerance = 0.25mm]

SDMMC1_CK_PB23
SDMMC1_CMD_PB22
SDMMC1_DAT0_PB24
SDMMC1_DAT1_PB25
SDMMC1_DAT2_PB26
SDMMC1_DAT3_PB27
SDMMC1_CD_PB29
SDMMC1_WP_PB28


50Ω ± 10% single-ended trace impedance

(3V3 / 1V8) VDDSDMMC1

VDD_3V3



VDD_3V3_SD



SDMMC1_CK_PB23

