

QSPI



Matched Net Lengths [Tolerance = 0.5mm]

QSPI0_IO0_PB11
QSPI0_IO1_PB10
QSPI0_IO2_PB9
QSPI0_IO3_PB8
QSPI0_SCK_PB13
QSPI0_CS_IN

50Ω ± 10% single-ended trace impedance

VDD_3V3

R132
10k
0402
1%

R133
10k
0402
1%

R134
10k
0402
1%

U9

SI/SIO0
SO/SIO1
WP/SIO2
HOLD/SIO3
SCK
CE

VDD
VSS
TPAD

SST26VF064BEUI-104I/MF

VDD_3V3

C125
0.1uF
16V
0402

GND

QSPI0_SCK_PB13

C126
50Ω
DNP

FB4

240R@100MHz
0402
DNP

GND

QSPI0_CS_PB12
QSPI0_CS_IN

1
2

J39

JP10



HDR-2.54 Male 1x2