

ATmega4809 - MFR - VAO

AVR® product family

Flash size in KB

Series name

Pin count

9 = 48 pins (PDIP: 40 pins)

8 = 32 pins (SSOP: 28 pins)

Variant Suffix

VAO = Automotive

Blank = Industrial

Carrier Type

R = Tape & Reel

Blank = Tube or Tray

Temperature Range

F = -40°C to +125°C (extended)

U = -40°C to +85°C (industrial)

Package Type

A = TQFP

M = VQFN

P = PDIP

X = SSOP