

- ▶ LINK LAM
- Loop Protection
- ▶ Spanning Tree
- ▶ IPMC Profile
- MVR
- ▶ IPMC
- ▶ LLDP
- PoE
- SyncE
- MAC Table
- ▼ VLANs
 - Configuration
 - SVL
- ▶ VLAN Translation
- ▶ Private VLANs
- ▶ VCL
- ▶ Voice VLAN
- ▶ QoS
- ▼ TSN
 - Streams
 - PTP check
 - Frame Preemption
 - ▼ TAS
 - Ports
 - Max SDU
- ▼ PSFP
 - Flow Meter
 - Stream Filter
 - Stream Gate
- FRER
- Mirroring
- UPnP
- PTP
- ▶ MRP
- ▶ CVDP

Global VLAN Configuration

Allowed Access VLANs	1
Ethertype for Custom S-ports	88A8

Port VLAN Configuration

Port	Mode	Port VLAN	Port Type	Ingress Filtering	Ingress Acceptance	Egress Tagging	Allowed VLANs	Forbidden VLANs
*	<>	1	<>	<input type="checkbox"/>	<>	<>	1-4095	
1	Hybrid	1	C-Port	<input type="checkbox"/>	Tagged and Untagged	Untag Port VLAN	1-4095	
2	Hybrid	1	C-Port	<input type="checkbox"/>	Tagged and Untagged	Untag Port VLAN	1-4095	
3	Access	1	C-Port	<input checked="" type="checkbox"/>	Tagged and Untagged	Untag All	1	
4	Access	1	C-Port	<input checked="" type="checkbox"/>	Tagged and Untagged	Untag All	1	
5	Access	1	C-Port	<input checked="" type="checkbox"/>	Tagged and Untagged	Untag All	1	
6	Access	1	C-Port	<input checked="" type="checkbox"/>	Tagged and Untagged	Untag All	1	
7	Access	1	C-Port	<input checked="" type="checkbox"/>	Tagged and Untagged	Untag All	1	
8	Access	1	C-Port	<input checked="" type="checkbox"/>	Tagged and Untagged	Untag All	1	

Save Reset