

	Frequency	Trace 1	Trace 2	
Cursor 1	12.79 Hz	12.222 dB	-553.164 m°	
Cursor 2	6.769 kHz	9.199 mdB	-88.584 °	
Delta C2-C1	6.756 kHz	-12.213 dB	-88.031 °	

