

Symbol	Description	Min.	Typ.	Max.	Unit
t_{start}	Start-up time	-	25	-	μs
$V_{\text{DDINT055V}}$	Power supply voltage range for INT055V	1.8	-	5.5	V
V_{DDINT11V}	Power supply voltage range for INT11V	1.8	-	5.5	
V_{DDINT15V}	Power supply voltage range for INT15V	1.9	-	5.5	
V_{DDINT25V}	Power supply voltage range for INT25V	2.9	-	5.5	
V_{DDINT43V}	Power supply voltage range for INT43V	4.75	-	5.5	