

AT28 BV 64B - 20 J U - T

AT28 = Parallel EEPROM

BV = 2.7V to 3.6V
(battery voltage)

64 = 64-Kbit Size

B = Revision

20 = 200 ns Speed

Blank = Tube Shipping
T = Tape and Reel Shipping

U = -40°C to +85°C Industrial Temperature Grade, 100% Matte Sn Terminal Finish

J = 32-Lead, Plastic J-Leaded Chip Carrier (PLCC)
S = 28-Lead, 0.300" Wide, Plastic Gull Wing Small Outline (SOIC)