



**Typical values (recommended):**

$C_1$ : 100 nF (primary decoupling capacitor)

$C_2$ : 1-10 nF (HF decoupling capacitor)

$C_3^{(*)}$ : 1  $\mu$ F (decoupling capacitor - optional)