

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|--------|-----|--------|--------|--------|-------|-----|-------------|-----|
| | | CMP2EN | CMP1EN | CMP0EN | ALUPD | | WGMODE[2:0] | |
| Access | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| Reset | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |

bits 2:0 WGMODE[2:0]: Waveform Generation Mode bits

These bits select the Waveform Generation mode.

| Value | Name | Description |
|-------|-------------|-----------------------|
| 0x0 | NORMAL | Normal Operation mode |
| 0x1 | FRQ | Frequency mode |
| 0x3 | SINGLESLOPE | Single-Slope PWM mode |
| 0x5 | DSTOP | Dual-Slope PWM mode |
| 0x6 | DSBOTH | Dual-Slope PWM mode |
| 0x7 | DSBOTTOM | Dual-Slope PWM mode |
| Other | - | Reserved |