

A T 2 5 0 1 0 B - S S P D - T

Product Family

25 = Standard SPI
Serial EEPROM

Device Density

010 = 1-Kilobit
020 = 2-Kilobit
040 = 4-Kilobit

Device Revision

Shipping Carrier Option

T = Tape and Reel, Standard Quantity Option
E = Tape and Reel, Extended Quantity Option

Operating Voltage

M = 1.7V to 5.5V
D = 2.5V to 5.5V

**Device Grade or
Wafer/Die Thickness**

P = Automotive Grade 1 (-40°C to +125°C)
9 = Automotive Grade 3 (-40°C to +85°C)

Package Option

SS = SOIC
X = TSSOP
MA = 2.0 mm x 3.0 mm UDFN