



Channel	Signal Name	Scale	Offset	Bandwidth	DC Coupling	Probe
C1	PWM_H_L1	2 V	-6.06 V	20 MHz	DC 1MΩ	10:1
C2	GPIO_Y_H	2 V	-4.88 V	20 MHz	DC 1MΩ	10:1
C3	V-AC	100 V	0 V	20 MHz	DC 1MΩ	RT-ZHD15
C4	I-AC	10 A	0 A	20 MHz	DC 1MΩ	RT-ZHD15
C5	ZC_Range	1 V	2.02 V	20 MHz	DC 1MΩ	10:1
C6	V(N-DGND)	200 V	0 V	20 MHz	DC 1MΩ	RT-ZHD15
C7	PWM_H_N	2 V	7.64 V	20 MHz	DC 1MΩ	10:1
C8	I-PE	200 mA	0 A	20 MHz	DC 1MΩ	User-Defined