



1 **C4** RMS: 58.8 V 2 **C8** RMS: 737.76 mA

C1- PWM L L1	C2- GPIO Y L	C3- I/P AC Cur	C4- I/P AC Vol	C5- Zero Cross f	C6- N - PE	C7- PWM L N	C8- FB AC N
4 V/ 10 MHz DC 1M Ω 10:1 -15.28 V	4 V/ 10 MHz DC 1M Ω 10:1 -8.92 V	10 A/ 10 MHz DC 1M Ω RT-ZC15B 0 V	200 V/ 10 MHz DC 1M Ω RT-ZHD15 7.8 V	2 V/ 10 MHz DC 1M Ω RT-ZHD15 10:1 202 V	100 v/ 10 MHz DC 1M Ω RT-ZHD15 10:1 202 V	2 V/ 10 MHz DC 1M Ω 10:1 7.86 V	2 V/ 10 MHz DC 1M Ω 10:1 -4.4 V