


39-Lead Wireless Module (2XW) - 15.5x20.7x2.8 mm Body [MODULE]
With Metal Shield and Coaxial Connector

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N	39		
Terminal Pitch	e	1.00 BSC		
Overall Height	A	2.60	2.80	3.00
PCB Thickness	A2	0.70	0.80	0.90
Shield Height	A3	1.90	2.00	2.10
UFL Connector Height	A4	1.25 REF		
Overall Length	D	15.40	15.50	15.60
Overall Width	E	20.60	20.70	20.80
Shield Length	D1	14.60	14.70	14.80
Shield Length	D2	7.99	8.09	8.19
Shield Width	E1	14.28	14.38	14.48
Shield Width	E2	11.58	11.68	11.78
Terminal Width	b	0.50	0.60	0.70
Terminal Length	L	0.70	0.80	0.90