

AT28 LV 010 - 20 T U

AT28 = Parallel EEPROM

LV = 3.3V

010 = 1 Mbit Size

U = -40°C to +85°C Industrial Temperature Grade, Matte Sn Terminal Finish

J = 32-Lead, Plastic J-leaded Chip Carrier (PLCC)

T = 32-Lead, Plastic Thin Small Outline Package (TSOP)

20 = 200 ns Speed