

Name	Sense	Value	Unit	Plot
BNC at Test Point 4	17	13.7	mV	☐
POT 1 at Test Point 6	2152	1.73	V	☐
POT 2 at Test Point 12	2070	1.67	V	☐
LED Status	2	2		☐
Voltage Ref	444	44.4	V	☐
Digital Test Points	2048	2048		☐
Digital Test Points 2	3	3		☐