


30-Lead Wireless Module (ZRX) - 13.4x18.7X2.8 mm Body [Module] With Metal Shield and Coaxial Connector

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



		Units	MILLIMETERS		
Dimension Limits			MIN	NOM	MAX
Number of Terminals	N		30		
Terminal Pitch	e		1.00 BSC		
Overall Height	A	2.60	2.80	3.00	
PCB Thickness	A2	0.70	0.80	0.90	
Shield Height	A3	1.90	2.00	2.10	
UFL Connector Height	A4		1.25 REF		
Overall Length	D	13.30	13.40	13.50	
Overall Width	E	18.60	18.70	18.80	
Shield Length	D1	12.14	12.24	12.34	
Shield Length	D2	6.60	6.70	6.80	
Shield Width	E1	12.14	12.24	12.34	
Shield Width	E2	8.92	9.02	9.12	
Terminal Width	b	0.50	0.60	0.70	
Terminal Length	L	0.70	0.80	0.90	

Notes:

1. All Dimensions are in Millimeters

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.