

A T 3 4 C 0 2 D - M A H M - T

Product Family

34C = I²C-compatible
Serial Presence Detect (SPD)
Serial EEPROM

Device Density

02 = 2 Kilobit

Device Revision

Shipping Carrier Option

T = Tape and Reel, Standard Quantity Option
E = Tape and Reel, Extended Quantity Option
B = Bulk (Tubes)

Operating Voltage

M = 1.7V to 5.5V

**Device Grade or
Wafer/Die Thickness**

H or U = Industrial Temperature Range
(-40°C to +85°C)
11 = 11mil Wafer Thickness

Package Option

SS = SOIC
X = TSSOP
MA = 2.0 mm x 3.0 mm UDFN
C = VFBGA
WWU = Wafer Unsawn