

SDMMC

Matched Net Lengths [Tolerance = 0.25mm]

▲ $50\Omega \pm 10\%$ single-ended trace impedance
Routing top or bottom

- SDMMC0_DAT3_PA20
- SDMMC0_CMD_PA16
- SDMMC0_CLK_PA17
- SDMMC0_DAT0_PA15
- SDMMC0_DAT1_PA18
- SDMMC0_DAT2_PA19
- SDMMC0_CD_PA23

