



Measure	P1:max(C1)	P2:max(C2)	P3:duty(C2)	P4:max(C3)	P5:max(C4)	P6:---
value	5.20 V	742 mV	--	33 mV	123 mV	--
status	✓	✓	✗	✓	✓	

C1	BwL	DC1M	C2	BwL	DC1M	C3	BwL	DC1M	C4	BwL	DC1M
2.00 V/div			500 mV/div			500 mV/div			200 mV/div		
-6.00 V ofst			500 mV ofst			500 mV ofst			205 mV ofst		

Timebase	0 μs	Trigger	C1	DC
100 kS	100 μs/div	Stop	1.38 V	
	100 MS/s	Edge	Positive	