



Measure	P1:max(C1)	P2:max(C2)	P3:duty(C2)	P4:max(C3)	P5:max(C4)	P6:---
value	5.20 V	5.15 V	99.414 %	13.35 V	3.32 V	---
status	✓	✓	✓	✓	✓	
C1	C2	C3	C4			
BwL DC1M	BwL DC1M	BwL DC1M	BwL DC1M			
5.00 V/div	5.00 V/div	10.0 V/div	1.000 V/div			
5.00 V offset	4.95 V offset	20.15 V offset	-2.985 V ofst			

Timebase -4.12 ms	Trigger C1 DC
2.00 ms/div	Stop 1.40 V
100 kS	5 MS/s
	Edge Positive