



Measure	P1:duty(C1)	P2:freq(C1)	P3:max(C2)	P4:max(C3)	P5:max(C4)	P6:---
value	36.470 %	501.505 kHz	675 mV	3.42 V	625 mV	---
status	✓	✓	✓	✓	✓	---

C1	BwL	DC1M	C2	BwL	DC1M	C3	BwL	DC1M	C4	BwL	DC1M
5.00 V/div			200 mV/div			2.00 V/div			200 mV/div		
-14.75 V ofst			5 mV offset			-5.90 V offset			5 mV offset		

Timebase	20 ns	Trigger	C1	DC
1.00 μs/div		Stop		200 mV
20 kS		Edge		Positive
2 GS/s				