



Measure	P1:duty(C1)	P2:freq(C1)	P3:duty(C2)	P4:max(C3)	P5:max(C4)	P6:- - -
value	59.896 %	501.756 kHz	37.254 %	13.2 V	3.37 V	---
status	✓	✓	✓	✓	✓	
C1	C2	C3	C4			
BwL DC1M	BwL DC1M	BwL DC1M	BwL DC1M			
5.00 V/div	5.00 V/div	5.00 V/div	2.00 V/div			
-14.75 V ofst	-14.65 V ofst	5.05 V offset	4.00 V offset			

Timebase	1.04 μ s	Trigger	C1 DC
	1.00 μ s/div	Stop	200 mV
20 kS	2 GS/s	Edge	Positive