



Measure	P1:duty(C1)	P2:freq(C1)	P3:duty(C2)	P4:max(C3)	P5:max(C4)	P6:---
value	36.426 %	501.509 kHz	59.801 %	3.40 V	3.33 V	---
status	✓	✓	✓	✓	✓	---

C1	BwL	DC1M	C2	BwL	DC1M	C3	DC1M	C4	BwL	DC1M
2.00 V/div			2.00 V/div			2.00 V/div		2.00 V/div		
-5.90 V offset			-5.95 V offset			0.00 V offset		4.00 V offset		

Timebase	20 ns	Trigger	C1 DC
	1.00 μs/div	Stop	2.86 V
20 kS	2 GS/s	Edge	Positive