

SUPC

 VDD Brown-Out Detector (BOD) Configuration

 Voltage Regulator (VREG) Configuration

 Voltage Reference (VREF) Configuration

 Enable Voltage Reference Output ☒

 Select Reference Voltage Level

4.096V voltage reference typical value 

 Enable On demand

1.024V voltage reference typical value

 Enable Temperature Sensor

2.048V voltage reference typical value

 Run in Standby mode

4.096V voltage reference typical value

☐