



8 Layer Stack Legend

	Material	Layer	Thickness	Dielectric Material	Type
		Top Overlay			Legend
	Surface Material	Top Solder	0.020mm	Solder Resist	Solder Mask
	Copper	L1 - Top	0.035mm		Signal
	Prepreg		0.085mm	1 x 1080	Dielectric
	Copper	L2 - GND	0.035mm		Signal
	Core		0.127mm	FR-4	Dielectric
	Copper	L3 - Signal	0.035mm		Signal
	Prepreg		0.381mm	3 x 2116	Dielectric
	Copper	L4 - PWR	0.035mm		Signal
	Core		0.127mm	FR-4	Dielectric
	Copper	L5 - Signal	0.035mm		Signal
	Prepreg		0.381mm	3 x 2116	Dielectric
	Copper	L6 - Signal	0.035mm		Signal
	Core		0.127mm	FR-4	Dielectric
	Copper	L7 - GND	0.035mm		Signal
	Prepreg		0.085mm	1 x 1080	Dielectric
	Copper	L8 - Bottom	0.035mm		Signal
	Surface Material	Bottom Solder	0.020mm	Solder Resist	Solder Mask
		Bottom Overlay			Legend

Total thickness: 1.60 mm $\pm$ 10%