

A T 2 4 C 1 2 8 C - S S H M x x - B

Product Family

24C = Standard I²C-compatible
Serial EEPROM

Device Density

128 = 128 Kilobit

Device Revision

Shipping Carrier Option

B = Bulk (Tubes)

T = Tape and Reel, Standard Quantity Option

E = Tape and Reel, Extended Quantity Option

Product Variation

xx = Applies to select packages only.

Operating Voltage

M = 1.7V to 5.5V

**Device Grade or
Wafer/Die Thickness**

H or U = Industrial Temperature Range
(-40°C to +85°C)

11 = 11mil Wafer Thickness

Package Option

SS = SOIC

X = TSSOP

MA = 2.0mm x 3.0mm UDFN

C = VFBGA

WWU = Wafer Unsawn

Note: Refer to automotive data sheet for automotive grade ordering information.