

500 $\pm$ 10% single-ended trace impedance

SDMMC0

Matched Net Lengths [Tolerance = 0.25mm]

SDMMC0_DAT0_PA0
SDMMC0_DAT1_PA3
SDMMC0_DAT2_PA4
SDMMC0_DAT3_PA5

SDMMC0_CLK_PA2
SDMMC0_CMD_PA1

SDMMC0_CD_PA23

R70
47k 1%
0402

R73
47k 1%
0402

R76
47k 1%
0402

R79
47k 1%
0402

R81
10k 1%
0402

R82
10k 1%
0402

VDD_3V3_PW_5D

VDD_3V3_PW_5D

VDD_3V3_PW_5D

J2

DAT0
DAT1
DAT2
CD/DAT3

CLK
CMD

SW_A
SW_B

VDD

VSS

GND

GND

GND

GND

P4

P6

G1

G2

G3

G6

DM3AT-SF-PEJM5

C9
0.1uF
50V
0402

GND

GND

GND