



Key:

C1: 0.1 μ F, 20V ceramic (recommended)

R1: 10 k Ω (recommended)

R2: 100 Ω to 470 Ω (recommended)

C2: 0.1 μ F, 20V ceramic (required)

C3: 0.1 μ F, 20V ceramic (required)