

A T 2 4 C M 0 2 - S S H D - B

Product Family
24C = Standard I²C-compatible
Serial EEPROM

Device Density
M = Megabit Family
02 = 2 Megabit

Shipping Carrier Option

B = Bulk (Tubes)
T = Tape and Reel, Standard Quantity Option
E = Tape and Reel, Extended Quantity Option

Operating Voltage

D = 2.5V to 5.5V
M = 1.7V to 5.5V

**Device Grade or
Wafer/Die Thickness**

H or U = Industrial Temperature Range
(-40°C to +85°C)
11 = 11mil Wafer Thickness

Package Option

SS = SOIC
U2 = WLCSP
WWU = Wafer Unsawn