

AT24C04D-SSHMXXT
Shipping Carrier Option
T = Tape and Reel, Standard Quantity Option
E = Tape and Reel, Extended Quantity Option
B = Bulk (Tubes)
Product Variation
xx = Applies to select packages only.
Operating Voltage
M = 1.7V to 3.6V
Device Grade or
Wafer/Die Thickness
H or U = Industrial Temperature Range
(-40°C to +85°C)
11 = 11mil Wafer Thickness
Package Option
P = PDIP
ST = SOT-23
SS = SOIC
X = TSSOP
MA = 2.0 mm x 3.0 mm UDFN
WWU = Wafer Unsawn
Product Family
24C = Standard I²C-compatible
Serial EEPROM
Device Density
04 = 4 Kilobits
Device Revision