

- IP Subnet-based VLAN
  - Voice VLAN
  - VoS
  - TSN
  - Mirroring
  - UPnP
  - PTP
  - MRP
  - GVRP
  - sFlow
  - DDMI
  - UDLD
- Monitor
  - System
  - Green Ethernet
  - Ports
    - State
    - Traffic Overview
    - QoS Statistics
    - QCL Status
    - Detailed Statistics
    - Name Map
  - CFM
  - APS
  - ERPS
  - Media Redundancy
  - Link OAM
  - DHCPv4
  - DHCPv6
  - Security
  - Aggregation
    - Loop Protection
  - Spanning Tree
    - MVR
    - IPMC
    - LLDP
  - PTP
    - PTP
    - 802.1AS Statistics
  - PoE
  - MAC Table
  - VLANs
  - MVRP
  - sFlow
  - DDMI

**PTP Clock's Configuration**

**Clock Type and Profile**

| Clock Instance | HW Domain | Device Type | Profile | Filter Type | Filter Mode |
|----------------|-----------|-------------|---------|-------------|-------------|
| 0              | 0         | P2pTransp   | 1588    | BASIC       | NONE        |

**Local Clock Current Time**

| PTP Time                              | Clock Adjustment method | Ports Monitor Page |
|---------------------------------------|-------------------------|--------------------|
| 2024-04-18T16:28:10+00:00 814,252,367 | Internal Timer          | Ports Monitor      |

**Clock Default Data Set**

| Device Type | One-Way | 2 Step Flag | Ports | Clock Identity          | Dom | Clock Quality             | Pri1 | Pri2 | Local Prio | Protocol | VID | PCP | DSCP |
|-------------|---------|-------------|-------|-------------------------|-----|---------------------------|------|------|------------|----------|-----|-----|------|
| P2pTransp   | False   | True        | 8     | 00:05:5a:ff:fe:a0:1a:13 | 0   | Cl:248 Ac:Unknwn Va:65535 | 128  | 128  | 128        | Ethernet | 1   | 0   | 0    |

**Clock Current Data Set**

| stpRm | Offset From Master | Mean Path Delay   | Slave Port | Slave State | Holdover(ppb) |
|-------|--------------------|-------------------|------------|-------------|---------------|
| 0     | 0.000,000,000,000  | 0.000,000,000,000 | 0          | FREERUN     | N.A.          |

**Clock Parent Data Set**

| Parent Port ID          | port | PStat | Var | Rate | GrandMaster ID          | GrandMaster Clock Quality | Pri1 | Pri2 |
|-------------------------|------|-------|-----|------|-------------------------|---------------------------|------|------|
| 00:05:5a:ff:fe:a0:1a:13 | 0    | False | 0   | 0    | 00:05:5a:ff:fe:a0:1a:13 | Cl:248 Ac:Unknwn Va:65535 | 128  | 128  |

**Clock Time Properties Data Set**

| UtcOffset | Valid | leap59 | leap61 | Time Trac | Freq Trac | ptp Time Scale | Time Source |
|-----------|-------|--------|--------|-----------|-----------|----------------|-------------|
| 0         | False | False  | False  | False     | False     | True           | 160         |

**Basic Filter Parameters**

| DelayFilter | Period | Dist |
|-------------|--------|------|
| 0           | 10     | 0    |

**Basic Servo Parameters**

| Display | P-enable | I-enable | D-enable | 'P' constant | 'I' constant | 'D' constant | Gain constant |
|---------|----------|----------|----------|--------------|--------------|--------------|---------------|
| False   | True     | False    | False    | 1            | 30           | 40           | 1             |