



	SYMBOL	MIN	NOM	MAX	
TOTAL THICKNESS	A	0.8	0.85	0.9	
STAND OFF	A1	0	0.035	0.05	
MOLD THICKNESS	A2	---	0.65	---	
L/F THICKNESS	A3	0.203 REF			
LEAD WIDTH	b	0.2	0.25	0.3	
BODY SIZE	X	9 BSC			
	Y	9 BSC			
LEAD PITCH	e	0.5 BSC			
EP SIZE	X	J	7.5	7.6	7.7
	Y	K	7.5	7.6	7.7
LEAD LENGTH	L	0.35	0.4	0.45	
PACKAGE EDGE TOLERANCE	aaa	0.1000			
MOLD FLATNESS	bbb	0.1000			
COPLANARITY	ccc	0.0800			
LEAD OFFSET	ddd	0.1000			
EXPOSED PAD OFFSET	eee	0.1000			
HALF-CUT DEPTH	R	0.1	0.125	0.15	
HALF-CUT WIDTH	S	---	---	0.04	

