

- ▶ VCL
- ▶ Voice VLAN
- ▶ QoS
- ▶ TSN
- ▶ Mirroring
- ▶ UPnP
- ▶ PTP
- ▶ MRP
- ▶ GVRP
- ▶ sFlow
- ▶ DDMI
- ▶ UDLD
- ▼ **Monitor**
  - ▶ System
  - ▶ Green Ethernet
  - ▼ Ports
    - State
    - Traffic Overview
    - QoS Statistics
    - QCL Status
    - Detailed Statistics
    - Name Map
  - ▶ CFM
  - ▶ APS
  - ▶ ERPS
  - ▶ Media Redundancy
  - ▶ Link OAM
  - ▶ DHCPv4
  - ▶ DHCPv6
  - ▶ Security
  - ▶ Aggregation
  - ▶ Loop Protection
  - ▶ Spanning Tree
  - ▶ MVR
  - ▶ IPMC
  - ▶ LLDP
  - ▼ PTP
    - PTP
    - 802.1AS Statistics
    - PoE
    - MAC Table
    - ▶ VLANs
    - MVRP
    - sFlow
    - ▶ DDMI
    - UDLD
    - ▶ TSN
  - ▼ **Diagnostics**
    - Ping (IPv4)
    - Ping (IPv6)

Auto-refr

**PTP Clock's Configuration**

**Clock Type and Profile**

Clock Instance	HW Domain	Device Type	Profile	Filter Type	Filter Mode
0	0	Slaveonly	1588	BASIC	PACKET

**Local Clock Current Time**

PTP Time	Clock Adjustment method	Ports Monitor Page
2024-04-18T14:21:33+00:00 385,585,953	Internal Timer	Ports Monitor

**Clock Default Data Set**

Device Type	One-Way	2 Step Flag	Ports	Clock Identity	Dom	Clock Quality	Pri1	Pri2	Local Prio	Protocol	VID	PCP	DSCP
Slaveonly	False	True	8	00:05:5a:ff:fe:a0:1a:13	0	Cl.255 Ac.Unkwnn Va.65535	255	128	128	Ethernet	1	0	0

**Clock Current Data Set**

stpRm	Offset From Master	Mean Path Delay	Slave Port	Slave State	Holdover(ppb)
1	0.000,000,003.559	0.000,000,000,000	1	PHASE_LOCKED	N.A.

**Clock Parent Data Set**

Parent Port ID	port	PStat	Var	Rate	GrandMaster ID	GrandMaster Clock Quality	Pri1	Pri2
ac:de:48:00:00:00:00:00	1	False	0	0	ac:de:48:00:00:00:00:00	Cl.248 Ac:1 us Va.65535	128	128

**Clock Time Properties Data Set**

UtcOffset	Valid	leap59	leap61	Time Trac	Freq Trac	ptp Time Scale	Time Source
36	True	False	False	False	False	True	160

**Basic Filter Parameters**

DelayFilter	Period	Dist
0	10	0

**Basic Servo Parameters**

Display	P-enable	I-enable	D-enable	'P' constant	'I' constant	'D' constant	Gain constant
False	True	False	False	1	30	40	1