

A	GND	PB9	PB10	PB13	PB7	PB20	PB21	PB24	D11	NWR1	A12	A6	A2	DDR_VREF	SDCK	GND
B	PB17	PB16	GND_ANA	PB15	PB23	PB22	DDR_CAL		D13	A0	A13	A4	GND	SD_CKN		A7
C	PB1	PB12	VDD_ANA	ADV_REFN	PB19	VDD_QSPI	DQM1		D15	VDD_IOM	A10	CAS	VDD_IOM		A14	A18
D	PB3	PB6	PB2	ADV_REFP	PB11		D9		DQS1		D14	SDA10		A9	A3	SDWE
E	PB5	PB25	PB4	PB18	PB8	GND	NWR0		ND_QS1	GND	A5		A11	A16	RAS	NCS1
F	PA28	PB14	TDI	PB0	TMS	VDD_CORE	PA26	PA24	D10	D12	VDD_CORE	NRD	SD_CKE	A17	NCS0	A8
G	PA22	PA30	VDD_IOP6		GND	PA21		PA9	D8		DQM0	GND		VDD_IOM	A15	A1
H	PA25	PA27	PA29	PA31	TDO	PA15	PA11	GND	GND	D1	D3	DQS0	ND_QS0	A19	D2	D0
J	PA18	PA20	PA17	PA23	PA19	PA13	PC15	GND	GND	PD9	D5	PD7	D7	D4	PD13	D6
K	PA14	PA16	VDD_IOP6		GND	PA7		PC17	PC23		PD11	GND		VDD_NF	PD8	PD6
L	PA12	PA10	PA3	PA5	PC4	VDD_CORE	PC13	PC19	PC25	PC29	VDD_IN33	PD14	PD18	NWR3	PD12	PD10
M	PA8	PA6	PA1	PC0		PC6	GND	PC21	PC27	GND_IN33	PD20		PC31	PD16	PD21	PD15
N	PA4	GND	VDD_IOP1		PC2	PC11		PC8	PC28		PD5	HS_DMC		PD3	GND	PD17
P	PA2	PA0		PC1	PC3	PC10	VDD_BU	PC20	JTAG_SEL	VDD_OUT25	RTU_NE	HS_DPC	VDD_IN33		PD2	PD19
R	NRST		TCK	PC5	PC12	PC16	PC22	PC24	XOUT_32	XIN	SHDN	HS_DMA	GND_IN33	PD0		PD4
T	GND	RTCK	PC7	PC9	PC14	PC18	PC30	PC26	XIN_32	XOUT	WK_UPD	HS_DPA	HS_DPB	HS_DMB	PD1	GND



1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16