





[illegible]


DEBUGGER




DEBUGGER TESTPOINT




DEBUGGER POWER/STATUS LED



DEBUGGER USB MICRO-B CONNECTOR



ID PIN



<i>Interface</i> <i>Signal</i>	ICSP TARGET	UPDI TARGET
CDC TX	UART RX	UART RX
CDC RX	UART TX	UART TX
DBG0	DAT	UPDI
DBG1	CLK	GPIO
DBG2	GPIO	GPIO
DBG3	<u>MCLR</u>	<u>RESET</u>
VCC	-	-

MIC5528:
Vin: 2.5V to 5.5V
Vout: Fixed 1.2V
Imax: 500mA
Dropout: 200mV