

- Support Overview
- VLAN

- Voice VLAN
- QoS
- TSN
- Mirroring
- UPnP
- PTP
- MRP
- GVRP
- sFlow
- DDMI
- UDLD

#### Monitor

- System
- Green Ethernet
- Ports
  - State
  - Traffic Overview
  - QoS Statistics
  - OCL Status
  - Detailed Statistics
  - Name Map
- CFM
- APS
- ERPS
- Media Redundancy
- Link OAM
- DHCPv4
- DHCPv6
- Security
- Aggregation
- Loop Protection
- Spanning Tree
- MVR
- IPMC
- LLDP
- PTP
  - 802.1AS Statistics
- PoE
- MAC Table
- VLANs
- MVRP
- sFlow
- DDMI

### PTP Clock's Configuration

#### Clock Type and Profile

Clock Instance	HW Domain	Device Type	Profile	Filter Type	Filter Mode
0	0	P2pTransp	1588	BASIC	NONE

#### Local Clock Current Time

PTP Time	Clock Adjustment method	Ports Monitor Page
2024-04-18T16:28:10+00:00 814,252,367	Internal Timer	Ports Monitor

#### Clock Default Data Set

Device Type	One-Way	2 Step Flag	Ports	Clock Identity	Dom	Clock Quality	Pri1	Pri2	Local Prio	Protocol	VID	PCP	DSCP
P2pTransp	False	True	8	00:05:5a:ff:fe:a0:1a:13	0	Cl:248 Ac:Unknwn Va:65535	128	128	128	Ethernet	1	0	0

#### Clock Current Data Set

stpRm	Offset From Master	Mean Path Delay	Slave Port	Slave State	Holdover(ppb)
0	0.000,000,000,000	0.000,000,000,000	0	FREERUN	N.A.

#### Clock Parent Data Set

Parent Port ID	port	PStat	Var	Rate	GrandMaster ID	GrandMaster Clock Quality	Pri1	Pri2
00:05:5a:ff:fe:a0:1a:13	0	False	0	0	00:05:5a:ff:fe:a0:1a:13	Cl:248 Ac:Unknwn Va:65535	128	128

#### Clock Time Properties Data Set

UtcOffset	Valid	leap59	leap61	Time Trac	Freq Trac	ptp Time Scale	Time Source
0	False	False	False	False	False	True	160

#### Basic Filter Parameters

DelayFilter	Period	Dist
0	10	0

#### Basic Servo Parameters

Display	P-enable	I-enable	D-enable	'P' constant	'I' constant	'D' constant	Gain constant
False	True	False	False	1	30	40	1