



**Key:**

C1: 0.1  $\mu$ F, 20V ceramic (recommended)

R1: 10 k $\Omega$  (recommended)

R2: 100 $\Omega$  to 470 $\Omega$  (recommended)

C2: 0.1  $\mu$ F, 20V ceramic (required)