




Matched Net Lengths [Tolerance = 1mm]

UIE




Matched Net Lengths [Tolerance = 1mm]



500 ± 10% single-ended trace impedance
Routing top or bottom


1000 ± 10% differential trace impedance
Routing top or bottom

Matched Net Lengths [Tolerance = 1mm]




500 ± 10% single-ended trace impedance
Routing top or bottom

1000 ± 10% differential trace impedance
Routing top or bottom



DDR_VREF



MT41K128M16JT-125 AAT-K

