


# 48-Lead Very Thin Plastic Quad Flat, No Lead Package (SLB) - 7x7 mm Body [VQFN] With 5.6x5.6 mm Exposed Pad and Stepped Wettable Flanks

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



		Units	MILLIMETERS		
Dimension Limits			MIN	NOM	MAX
Number of Terminals	N		48		
Pitch	e		0.50 BSC		
Overall Height	A	0.80	0.90	1.00	
Standoff	A1	0.00	0.035	0.05	
Terminal Thickness	A3	0.203 REF			
Wettable Flank Step Cut Depth	A4	0.10	-	0.19	
Overall Length	D	7.00 BSC			
Exposed Pad Length	D2	5.50	5.60	5.70	
Wettable Flank Step Cut Width	D3	-	-	0.085	
Overall Width	E	7.00 BSC			
Exposed Pad Width	E2	5.50	5.60	5.70	
Terminal Width	b	0.20	0.25	0.30	
Terminal Length	L	0.35	0.40	0.45	
Terminal-to-Exposed-Pad	K	0.20	-	-	

**Notes:**

- Pin 1 visual index feature may vary, but must be located within the hatched area.
- Package is saw singulated
- Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.