


82L-PCB Module (6TW) - 19x25x2.75 mm - [MODULE] with Metal Shield and Coaxial Connector

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N	82		
Terminal Pitch	e	1.27 BSC		
Overall Height	A	2.60	2.75	2.90
PCB Thickness	A2	0.70	0.80	0.90
Shield Height	A3	1.80	1.85	1.90
Coaxial Connector Height	A4	1.25 REF		
Overall Length	D	18.90	19.00	19.10
Overall Width	E	24.90	25.00	25.05
Shield Length	D1	17.45	17.50	17.55
Shield Width	E1	18.74	18.79	18.84
Terminal Width	b	0.50	0.60	0.70
Terminal Length	L	0.70	0.80	0.90

Notes:

- 1. All Dimensions are in Millimeters
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
REF: Reference Dimension, usually without tolerance, for information purposes only.