



— Typical 25°C — Max. (Typical -40°C + 3σ)

Vdd	Typical 25	Typical -40	1 sigma	Vdd	Typical 25°	Max. (Typical -40°C + 3σ)
1.8	5.76E-05	5.71E-05	2.25E-06	1.8	57.59475	63.88451
1.82	5.78E-05	5.77E-05	2.32E-06	1.82	57.75961	64.71471
1.84	5.81E-05	5.82E-05	2.39E-06	1.84	58.05	65.42642
1.86	5.83E-05	5.87E-05	2.46E-06	1.86	58.30044	66.03688
1.88	5.85E-05	5.9E-05	2.51E-06	1.88	58.50031	66.54507
1.9	5.87E-05	5.93E-05	2.56E-06	1.9	58.67086	66.95529
1.92	5.88E-05	5.95E-05	2.59E-06	1.92	58.80162	67.29103
1.94	5.89E-05	5.97E-05	2.63E-06	1.94	58.91604	67.5621
1.96	5.9E-05	5.98E-05	2.65E-06	1.96	59.00378	67.76509
1.98	5.91E-05	5.99E-05	2.68E-06	1.98	59.07899	67.95962
2	5.91E-05	6E-05	2.69E-06	2	59.13789	68.07651
2.02	5.92E-05	6.01E-05	2.7E-06	2.02	59.18906	68.19858
2.04	5.92E-05	6.01E-05	2.72E-06	2.04	59.23487	68.28809
2.06	5.93E-05	6.02E-05	2.72E-06	2.06	59.27368	68.35004
2.08	5.93E-05	6.02E-05	2.73E-06	2.08	59.3035	68.41497
2.1	5.93E-05	6.03E-05	2.73E-06	2.1	59.33142	68.46473
2.12	5.94E-05	6.03E-05	2.73E-06	2.12	59.35035	68.50064
2.14	5.94E-05	6.03E-05	2.74E-06	2.14	59.37221	68.5352
2.16	5.94E-05	6.03E-05	2.74E-06	2.16	59.38878	68.57677
2.18	5.94E-05	6.04E-05	2.75E-06	2.18	59.40421	68.61231
2.2	5.94E-05	6.04E-05	2.75E-06	2.2	59.41857	68.63833
2.22	5.94E-05	6.04E-05	2.75E-06	2.22	59.42835	68.65284
2.36	5.95E-05	6.05E-05	2.76E-06	2.36	59.49199	68.75096
2.46	5.95E-05	6.05E-05	2.76E-06	2.46	59.52145	68.78319
2.56	5.96E-05	6.05E-05	2.76E-06	2.56	59.55463	68.82922
2.66	5.96E-05	6.06E-05	2.76E-06	2.66	59.57715	68.87325
2.76	5.96E-05	6.06E-05	2.76E-06	2.76	59.59244	68.88806
2.86	5.96E-05	6.06E-05	2.76E-06	2.86	59.61428	68.92342
2.96	5.96E-05	6.07E-05	2.76E-06	2.96	59.62454	68.92689
3.06	5.96E-05	6.07E-05	2.76E-06	3.06	59.64199	68.95281
3.16	5.97E-05	6.07E-05	2.76E-06	3.16	59.65535	68.96408
3.32	5.97E-05	6.07E-05	2.76E-06	3.32	59.67475	69.01701
3.48	5.97E-05	6.07E-05	2.77E-06	3.48	59.69795	69.04799
3.62	5.97E-05	6.08E-05	2.77E-06	3.62	59.71353	69.06881
3.76	5.97E-05	6.08E-05	2.77E-06	3.76	59.74012	69.08393
3.84	5.98E-05	6.08E-05	2.76E-06	3.84	59.7511	69.07235
4.02	5.98E-05	6.08E-05	2.77E-06	4.02	59.76562	69.11398
4.18	5.98E-05	6.08E-05	2.77E-06	4.18	59.78668	69.15747
4.36	5.98E-05	6.09E-05	2.77E-06	4.36	59.81664	69.17112
4.48	5.98E-05	6.09E-05	2.78E-06	4.48	59.82739	69.20499
4.64	5.98E-05	6.09E-05	2.77E-06	4.64	59.84793	69.21482
4.76	5.99E-05	6.09E-05	2.77E-06	4.76	59.86321	69.21558
4.88	5.99E-05	6.09E-05	2.77E-06	4.88	59.88528	69.23697
5	5.99E-05	6.09E-05	2.77E-06	5	59.90193	69.24957

5.12	5.99E-05	6.1E-05	2.77E-06	5.12	59.91776	69.26995
5.2	5.99E-05	6.1E-05	2.77E-06	5.2	59.93064	69.28367
5.32	6E-05	6.1E-05	2.76E-06	5.32	59.95729	69.29209
5.38	6E-05	6.1E-05	2.77E-06	5.38	59.9739	69.32701
5.5	6E-05	6.12E-05	2.78E-06	5.5	60.0499	69.50883