





| VERSION CONTROL | | |
|-----------------|---------|---------------|
| VER | INITIAL | DESCRIPTION |
| 1 | VG | Final Release |



| INTERCONNECTS | | |
|---------------|-------------------|-------------------------|
| REF | TYPE | MFG PART NUMBER |
| J1, J4, J5 | Optical RX | HFBR-2531ETZ / FR05DVCR |
| J2, J3 | Optical TX | HFBR-1531ETZ / FT05MVNR |
| J6, J7 | Header 2x3 female | ESQ-103-33-L-D |
| J8 | Header 2x2 Female | ESQ-102-33-L-D |
| J9, J10 | Header 2x3 Male | TSW-103-23-F-D |

| | |
|----------------|---------------------------------------|
| NOTES | TOLERANCES UNLESS OTHERWISE SPECIFIED |
| | X = ±0.5 |
| | XX = ±0.25 |
| | XXX = ±0.13 |
| | BOARD THICKNESS BOARD OUTLINE |
| | 2.28 ± 0.254 X = ±0.1 |
| | COMPONENT HOLES AND MOUNTING HOLES |
| | ±0.381 ± 0.076 |
| | ±0.381 ± 0.127 |
| | HOLE M = IGBT MOUNTING HOLE |
| | HOLE F = FIXING HOLES |
| DRWN BY | DATE |
| Vipin G | 8/24/2023 |
| APPD BY | DATE |
| ** | 8/24/2023 |



MICROCHIP
Microchip Technology Inc.
2025 Washington Avenue
Philadelphia, PA 19146

| | |
|--|--------------------------|
| TITLE XIFM LinPak HV100 Control Board | |
| SIZE A4 | PART NO XIFM-CS |
| SCALE 1:1 | UNITS Millimeters |
| VER 1 | SHEET 1 of 1 |