

AT28 C 64B - 15 J U - T

AT28 = Parallel EEPROM

C = 4.5V to 5.5V

64 = 64-Kbit Size

B = Revision

15 = 150 ns Speed

WM = Die Sales (contact Microchip)

DWF = Wafer Sales (contact Microchip)

Blank = Tube Shipping

T = Tape and Reel Shipping

U = -40°C to +85°C Industrial Temperature Grade, 100% Matte Sn Terminal Finish

P = 28-Lead, Plastic Dual Inline Package (PDIP)

J = 32-Lead, Plastic J-Leaded Chip Carrier (PLCC)

S = 28-Lead, 0.300" Wide, Plastic Gull Wing Small Outline (SOIC)